



Offered in solid & hollow bars.

One of the finest powder metal bearings on the market. By using a proprietary blending and sintering process this gives us a uniform grain structure and spheroidized porosity which results in superior strength, lower coefficient of friction and a uniform oil coating of the mating shaft. During operation, oil impregnated bronzes have a proven record of excellent wear resistance and long life where normal lubrication is difficult or impossible to provide.

Sizes Available From NBM

SOLID BAR 1/4" - 8" diameter HOLLOW BAR thru 8" O.D.

The above are provided in 6 1/2" standard lengths.

FLATS, SPECIAL SHAPES, AND SHORTER LENGTHS
ARE AVAILABLE UPON REQUEST AND MADE TO ORDER.

Spec Equivalents

ASTM B-438 (Grade 1 Type 2) AMS 4805 SAE 841 MIL-B-5687D

Chemical Composition

	Cu	Fe	Pb	С	Sn	Zn
min/max	87.5-90.5	1.0	1	1.75	9.5-10.5	-
nominal	-	-	-	-	-	-

Note: Cu + Sum of Named Elements, 99.5% min.

Typical Uses

Aerospace

Materials for Aircraft and Space Vehicles

Automotive

Gears, Cams, Sprockets, Bushings, Sleeves

Other Industrial

Machinery Components, Self-lubricating Pump Parts, Turbine Blades, Office Machines, Home Appliances, Medical Equipment

Agricultural

Farm, Lawn and Garden Equipment



PO BOX 800818 HOUSTON, TX 77280 fax: 713-869-9124





SAE 841

SINTERED BRONZE / OIL IMPREGNATED

WWW.NBMMETALS.COM

LEADING MANUFACTURER & MASTER DISTRIBUTOR OF BRASS, BRONZE, & COPPER ALLOYS

Room Temp Tensile & Hardness Data

DENSITY	POROSITY	"K" STRENGTH	TENSILE STRENGTH	YIELD STRENGTH	ELONGATION	BRINELL
(GM PER CU.CM)	(% OIL BY VOL)	Constant	(PSI)	IN COMP. (PSI)	(% IN ONE IN)	(3000 KG)
6.4-6.8	19 min.	26,500	14,000	11,000	1%	

Note: Bearings may exhibit appreciable differences in properties due to size, shape, thickness, etc...

Benefits

- Tight tolerances allow for reduced shaft clearances and better press fits.
- Long lasting self lubrication provides an oil film for smooth start-ups
- Elimination of oil groove and oil hole
- Can be re-oiled when dry (submerse in SAE 30 motor oil for 72 hours at room temperature to replenish)



PO BOX 800818 HOUSTON, TX 77280 fax: 713-869-9124

